up with the 1 second mark on the timer face. 5.9 2.2<sub>2.4</sub> / 2.6 / 2.8 5.8 1.5 ` 5.7 3.1 3.2 2 DARKROOM 3.3 **AUTOMATION** 3.4 3 3.5 3.6 www.darkroomautomation.com © 2007 3.7 3.8 -5.5 3.9 -4.1. 5.4 4.2 4.3 5.3 4.5 5.2 4.6 5.1 4.7 4.8 4.9

'0' on the f-stop dial lines

Diameter = 5.25" for metal GraLab 300 Scale to 5.10" for the Time-O-Lite EZC-73 and 4.25" for the plastic GraLab